


LED Light Assembly Instruction

(for two post lifts with manual release)

1. Component description:


Item	Part No.	Name	Specification	QTY
1	201123	LED lights	DC24V, single wire 2*0.5 ² *5200mm(include adapter), color temperature 5000K, luminous flux 2480lm	1
2	201127	Magnetic clip		8
3	201129	Magnetic universal stand		4
4	201124	LED lights	DC24V, single wire 2*0.5 ² *300mm (include adapter), color temperature 5000K, luminous flux 2480lm	1
5	201126	T coupler	T coupler	1
6	480027	100V~240VAC power input	Wire#1: 2*1 ² *600mm (without adaptor) Wire#2: 2*0.5 ² *800mm (include adaptor) Isolated 24V constant voltage drive, input 100V~240VAC	1
7	201130	Screw	M3*5	4
8	201139	Power input installation plate		1
9	201128	Wire	2*0.5 ² *5000mm, include adapter and coupler (Only for clear-floor type)	1

2. Illustration of components:



3. LED Light Installation Diagrams:

Manual control base-plate 2 post lift



4. Wire connection diagrams for LED Light:

