


LED Light Assembly Instruction

(for four post lifts with manual release)

1. Component description:


Item	Number	Name	specification	QTY
1	420269	Magnetic seat		12
2	420264	LED lights	DC24V, single wire 2*0.5 ² *1200mm (include coupler), color temperature 5000K, luminous flux 2880lm	2
3	201127	Magnetic clip		11
4	420267	Wire	2*0.5 ² *1400mm, include adapter and coupler	1
5	420265	LED lights	DC24V, double wire: 2*0.5 ² *300mm (include adaptor), color temperature 5000K, luminous flux 2880lm	2
6	420268	T coupler	T coupler	1
7	201139	Power input installation plate		1
8	480027	100V~240VAC power input	Wire#1: 2*1 ² *500mm (without adaptor). Wire#2: 2*0.5 ² *300mm (include adaptor) Isolated 24V constant voltage drive,input 100V~240VAC	1
9	420270	Wire	2*0.5 ² *2100mm, include adapter and coupler	1
10	201130	Screw	M3*5	4

2. Illustration of components:



3. LED Light Installation Diagrams:

Remark: symmetrical install LED lights on both side of lifting platform.



4. Wire connection diagrams for LED Light:

